



FOKY8.E76360

Electromagnetic Interference Filters Certified For Canada - Component

[Page Bottom](#)

Electromagnetic Interference Filters Certified For Canada - Component

[See General Information for Electromagnetic Interference Filters Certified For Canada - Component](#)

SCHURTER AG

E76360

VIA SAN MARTINO 20

CASELLA POSTALE 1961

6850 MENDRISIO, SWITZERLAND

Appliance filter:

FKA,FKB,FKE,FKF,FKG,FKH,	
FKI, FKID ,FKS, FKSA,FKSB ,FKT,FKGD,FKHD	
all followed by a 2, followed by -45,-50	
or 55, followed by	
-1	250V ac, 50/60 Hz, 1A
-2	250V ac, 50/60 Hz, 2A
-4	250V ac, 50/60 Hz, 4A
-6	250V ac, 50/60 Hz, 6A
-10	250V ac, 50/60 Hz, 10A
all followed by /I, /I-K2, /I-S, /M5, /M5-K2, /M5-S or	
/M80, /M80-K2, /M80-S or/may also be provided with any two	
digit suffix 01-99, with or without suffix X1.	
FKE, FKF all followed by a 2, followed by -45	
-1	250V ac, 50/60 Hz, 1A
-2	250V ac, 50/60 Hz, 2A
-3	250V ac, 50/60 Hz, 3A
-4	250V ac, 50/60 Hz, 4A
-6	250V ac, 50/60 Hz, 6A
-10	250V ac, 50/60 Hz, 10A
all followed by /I-S, /M5-S or /M80-S	
or/may also be provided with any two digit suffix 01-99, with or without suffix X1	
FKO,FKP,FKQ,FKR,FKV,FKW,	
FKSO,FKSP,FKSQ,FKSR,FKSS,FKST,	
FKSU,FKSV all followed by a 2,	
followed by -45, -50, -55, followed by	
-1	250V ac, 50/60 Hz, 1A
-2	250V ac, 50/60 Hz, 2A

-4	250V ac, 50/60 Hz, 4A
-6	250V ac, 50/60 Hz, 6A
-10	250V ac, 50/60 Hz, 10A
followed by /I, /I-K2, /M5, /M5-K2 or /M80, /M80-K2	
or may also be provided with	
any two digit suffix 01-99,	
with or without suffix X1	
FSW2-65-10/0.5-K1	250V ac, 50/60 Hz, 10A

Models FMBC-0F31-1602, FMBC-0F31-1603.

Models FMBB-0116-0810, FMBB-0124-1210, FMBB-0131-1610, FMBB-0131-2510.

Models FMAB-0172-0270, FMAB-0172-0470, FMAB-0172-0670, FMAB-0172-1070, FMAB-0172-1670, FMAB-0672-0270, FMAB-0672-0672-0670, FMAB-0672-0670, FMAB-0672-1070, FMAB-0672-1670, FMAB-0772-0270, FMAB-0670, FMAB-0772-0670, FMAB-0772-1070, FMAB-0772-1670.

Models FMAB-0924-1210, FMAB-0924-2010, FMAB-0924-3010, FMAB-0929-5010.

Models FMLB-0109-0640, FMLB-0109-1040, FMLB-0109-1640, FMLB-0109-2040, FMLB-0609-0640, FMLB-0609-1040, FMLB-0609-1640, FMLB-0609-2040, FMLB-0709-0640, FMLB-0709-1040, FMLB-0709-1640, FMLB-0709-2040, FMLB-0141-0140, FMLB-0141-0240, FMLB-0141-0440, FMLB-0141-0640, FMLB-0141-1040, FMLB-0641-0140, FMLB-0641-0240, FMLB-0641-0440, FMLB-0641-0640, FMLB-0641-1040, FMLB-0741-0140, FMLB-0741-0240, FMLB-0741-0440, FMLB-0741-0640, FMLB-0741-1040, FMLB-0151-0610, FMLB-0151-1010, FMLB-0151-1610, FMLB-0151-2010, FMLB-0651-0610, FMLB-0651-1010, FMLB-0651-1610, FMLB-0651-2010, FMLB-0751-0610, FMLB-0751-1010, FMLB-0751-1610, FMLB-0751-2010.

Models FMW2-41-1/I, FMW2-41-1/M5, FMW2-41-1/M80, FMW2-41-1/Z, FMW2-41-3/I, FMW2-41-3/M5, FMW2-41-3/M80, FMW2-41-3/M80-R, FMW2-41-3/Z, FMW2-41-6/I, FMW2-41-6/M5, FMW2-41-6/M80, FMW2-41-6/Z, FMW2-41-10/I, FMW2-41-10/M5, FMW2-41-10/M80, FMW2-41-10/Z, FMW2-52-2/1.25, FMW2-52-6/0.5, FMW2-55-10/0.5, FMW2-55-10/5, FMW2-55-20/5, FSS2-55-1/0.5, FSS2-55-2/0.5, FSS2-65-3/0.5, FSS2-65-4/3, FSS2-65-6/3, FSS2-90-10/3, FSW2-65-3/0.5, FSW2-65-3/5, FSW2-65-6/0.5, FSW2-65-6/5, FSW2-65-10/0.5, FSW2-65-10/5.

Models FPP225-4/, FPP2-25-6/, FPP2-30-0.7/, FPP2-30-1/, FPP2-30-2/, FPP2-30-3/, FPP2-40-1/, FPP2-40-3/. All followed by a, M5 or M80; Cat. Nos. FPF2-40-1/a, FPF2-40-3/a, FPF2-48-1.5/a, FPF2-48-6/a, FPF2-80-10/a, FPF2-80-15/a, with or without suffix X1.

Models FMW2-150-4/I, FMW2-150-4/Z, FMW2-150-10/I, FMW2-150-10/Z, FMW2-200-30/I, FMW2-200-30/Z.

Models FPP2-45-0.5/, FPP2-45-0.8/, FPP2-45-1.0/, FPP2-45-1.6/, FPP2-45-2.5/, FPP2-45-4.0/, FPP2-45-6.5/. All followed by a or b, M5 or M80.

Models FGS2-44-1/, FGS2-44-2/, FGS2-44-4/, FGS2-44-6/, FGS2-44-10/. All followed by I, I-IF, I-IL, I-S, M5, M5-IF, M5-IL, M5-S or M80, M80-IF, M80-IL, M80-S.

Model FKE2-45-3/I-K1.



Marking: Company name, model designation and Recognized Component Mark for Canada

Last Updated on 2004-10-29

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2006 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner,

without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2006 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

