



# Datasheet



## RS 811-7064

Basic Vertical PDU with:-

- 12 x UK BS1363 Right Hand Angled Sockets
- Unit Switch
- EMI Filter
- 3 Metre Bottom Front Fed Lead
- 230V/13A UK BS1363 Plug
- Black Finish

### Specifications:

Quantity Of Inputs	1
Voltage	230V
Amperage	13A
VA per Input (Load Capacity)	2.9kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	Green neon with protective cover
Power Cable Wire Gauge	1.5mm <sup>2</sup> PVC
Power Cable Length	3m
Plug Type	BS 1363P
Receptacle/Socket Type #1	BS1363
Quantity on Face #1	12
Style #1	Individual - Right Hand Angled
Maximum Output per Receptacle/Socket #1	13A
Voltage per Receptacle/Socket #1	230V
Heavy Steel -Black Powder Coat	Yes
Configuration	39in / 978mm Vertical Rackmount
GE Vertical Mounting Bracket	Yes
Toolless Mounting Hardware - Center to Center Spacing	933.45 mm
Product Warranty	Lifetime
Certification/Agency Approvals	Complies with EN 60950
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	CE Marked
Chassis Dimensions (LxWxD)	978mm x 54mm x 51mm