

## Test plugs - MPS-MT SN - 3212251

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test plugs, tin-plated surface, Color: silver


The figure shows a similar product

### Why buy this product

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm diameter
- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided



### Key commercial data

Packing unit	1
GTIN	 4 046356 517393
Custom tariff number	85366990

### Technical data

Length	28.5 mm
Length contact range	10.85 mm
Pin diameter	2.30 mm
Note on dimensions	Length without insulating sleeve

### General

Color	silver
Material	Tin-plated brass
Minimum temperature	-40 °C
Maximum temperature	125 °C
Voltage	60 V DC
Additional text	30 V AC
Current	10 A

## Test plugs - MPS-MT SN - 3212251

### Classifications

#### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

#### ETIM

ETIM 3.0	EC002255
ETIM 4.0	EC002255
ETIM 5.0	EC002555

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411