

Contents

- The fiberglass reinforced cutting wheels are for cutting in all sorts of metals. Quick, Easy, Keyless.

Technical specifications

Shank diameter:

3,2 mm

Working diameter:

38,0 mm

Maximum RPM:

35.000 1/min

Quantity

12

Order number

2615S456JD

EAN-Code

8710364042845