






- 注;
1. 適用ハウジング型番 172280, 172281.
 2. 適用端子型番 170279, 170280.
 3. 適用製品規格 108-5136

単位: mm DIMENSIONS IN MM DO NOT SCALE FROM

				DRAWN BY AMP JAPAN, LTD. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING		参考図面 (CUSTOMER COPY) REFERENCE ONLY	
				MATERIAL: 7DD7LV (CR)		 日本ニール・エム・ピー株式会社 TOKYO, JAPAN	
				COLOR: 黒			
				SPECIFICATION: 0.5 ~ 2 mm AWG		JIS CLASS: //	
OPERATION DATA: AV 200V		JIS TYPE: //					
2 ~ 3.4 mm		JIS NO: //					
DATE: 11/16/84				TOLERANCE: ±0.4		JIS SCALE: 2:1	
EXCEPT AS NOTED				LOC: J		SIZE: AC-172282	
REV: 0				DATE: 11/16/84		REV: 0	
K. Oda 11/16/84				K. Oda 11/16/84		12極 Iコナール シリーズ J コネクター コム栓	