

EK EKOE 180 G



Sample photo

Order symbol: EKOE 180 G
Product nbr: 2538040
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013576
EI. number:
Finland: 3425419
Italy: 7501140
Sweden: 2538040
Norway:

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:	
mm:		280	280	180	Ingress Protection (EN 60529): IP 66/67	
inch:		11.0	11.0	7.1	Impact Resistance (EN 62262): IK 08	
Materials:						
Material:		Polycarbonate			Electrical insulation: Totally insulated	
Base colour:		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes	
Cover colour:		RAL 7035			UV resistance: UL 508	
Cover screws material:		Polyamide			Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws colour:		Grey			Glow Wire Test (IEC 695-2-1) °C: 960	
Gasket material:		Polyurethane			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Temperatures:						
Short term:		-40 ... 120 °C			Certificates: Germanischer Lloyd (GL) Underwriters Laboratories Det Norske Veritas Bureau Veritas Fimko Lloyds Register of Shipping (LR) Europe EN 62208: 2003 UL Canada Gost R	
Continuous:		-40 ... 80 °C				
Short term:		-40 ... 250 °F				
Continuous:		-40 ... 175 °F				
Accessories:						
EKOE		Base, PC				
EKO 30-G		Cover				
EKO 80-G		Cover				
EKO 30-T		Cover				
EKO 80-T		Cover				
EKOVT		Mounting plate				
EKOXT		Mounting plate Pertinax				
EKV 22		DIN-35 Mounting rail				
EKOZR		Extension frame				

