





Han® PushPull, type acc. to IEC 61 076-3-117 variant 14 Accessories

Identification	Part No.	Drawing	Dimensions in mm
<p>Han® PushPull dust protection cover IP 40 rubber (NBR) for device side</p>	09 35 002 5401		
<p>Han® PushPull protection cover IP 65 / IP 67 for device side</p> <p>without fixing cord</p>	09 35 002 5403 XL ¹⁾		
with fixing cord	09 35 002 5402 09 35 002 5402 XL ¹⁾		
with nylon fixing cord	09 35 002 5404 09 35 002 5404 XL ²⁾		
<p>Han® PushPull dust protection cover IP 40 for cable side</p>	09 35 002 5412		
<p>Han® PushPull protection cover IP 65 / IP 67 for cable side</p> <p>without fixing cord</p>	09 35 002 5411		
with nylon fixing cord	09 35 002 5413		

¹⁾ Packaging with 100 pieces
²⁾ Packaging with 250 pieces