

0603 sample kit					
NP0 50 V		NP0 25 V		X7R 16 V	
Capacitance (pF)	Tolerance	Capacitance (pF)	Tolerance	Capacitance (pF)	Tolerance
0.47	±0.25 pF	1 000	±5%	33 000	±10%
0.68	±0.25 pF	1 500	±5%	47 000	±10%
1	±0.25 pF	X7R 50 V		68 000	±10%
1.5	±0.25 pF	Capacitance (pF)	Tolerance	100 000	±10%
2.2	±0.25 pF	100	±10%	Y5V 50 V	
3.3	±0.25 pF	150	±10%	Capacitance (pF)	Tolerance
4.7	±0.25 pF	220	±10%	10 000	±20%
6.8	±0.50 pF	330	±10%	22 000	±20%
10	±5%	470	±10%	47 000	±20%
15	±5%	680	±10%	100 000	±20%
22	±5%	1 000	±10%	Y5V 16 V	
33	±5%	1 500	±10%	Capacitance (pF)	Tolerance
47	±5%	2 200	±10%	220 000	±20%
68	±5%	3 300	±10%	470 000	±20%
100	±5%	4 700	±10%		
150	±5%	6 800	±10%		
220	±5%	10 000	±10%		
330	±5%	X7R 25 V			
470	±5%	Capacitance (pF)	Tolerance		
680	±5%	15 000	±10%		
		22 000	±10%		

48 pieces per value; Ordering code: 432204407121.