

Datasheet

Item No. 92.238.6064.2

Cable assembly GST18I3K1-S 25H 60WS

Connection cable, male - free end, length 6m, GST18i3, 3 pole, 250 V, 20 A, cable type S05Z1Z1, halogen-free, cross section 2,5 mm², colour of coding: white, colour of cable: white

Item No.	92.238.6064.2
EAN	4015573705654
order unit	10 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Color of housing inclusive strain relief	White

Model

Number of poles	3
Nominal cross section conductor	2.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05Z1Z1-F
Cable colour	White
Cable diameter	10.2 mm
Version of cable	Male - free end
Cross section of cable 2	2.5 mm ²

Material

Surface finish	Tin-plated
Halogen free	Yes
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	6 m
--------------	-----

Drawings