


4

3

2

1

LOC —	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A	REVISED PER ECO-09-014471	18JUN09	HMR	CR	




CLAMPING SCREW



MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG

ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C



WIRE ENTRY



MATING FACE

60.96	16	1-1986375-6
57.15	15	1-1986375-5
53.34	14	1-1986375-4
49.53	13	1-1986375-3
45.72	12	1-1986375-2
41.91	11	1-1986375-1
38.10	10	1-1986375-0
34.29	9	1986375-9
30.48	8	1986375-8
26.67	7	1986375-7
22.86	6	1986375-6
19.05	5	1986375-5
15.24	4	1986375-4
11.43	3	1986375-3
7.62	2	1986375-2
DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 17MAR2008	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK C RICHARD 3/17/08				
		APVD C RICHARD 3/17/08	NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING, LEFT HAND, 3.81mm PITCH			
		PRODUCT SPEC	—			
MATERIAL —		APPLICATION SPEC	—			
		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986375	RESTRICTED TO —
FINISH —		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV A