

JB12-2

ABB contact for United
Kingdom

General Information

Extended Product Type:	JB12-2
Product ID:	1SNK912302R0000
EAN:	3472599123021
Catalog Description:	JB12-2 Jumper Bar - Orange
Long Description:	JB12-2 Jumper Bar - Orange - 12 mm 0.472 in spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472599123021
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	4.90 g
----------------------------	--------

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	45 mm
Package Level 1 Height:	45 mm
Package Level 1 Length:	105 mm
Package Level 1 Gross Weight:	0.293 kg
Package Level 1 EAN:	3472599123021
Package Level 2 Units:	1500 piece
Package Level 3 Units:	96000 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Orange
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting Type:	- In explosive atmospheres, the use of jumper bars with cut extremities and cut poles is not authorized; - in industrial use: additional accessories must be installed on the cut side of the jumper bar with cut extremities: - circuit separator CS when mounted on feed-through or ground terminal blocks.

Product Main Type:	JB12
Product Name:	Terminal Blocks Accessories
Rated Current (I_n):	Main Circuit 76 A
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Rated Voltage (U_r):	1000 V
Spacing:	12 mm
Sub-Function 2:	Screwless

Certificates and Declarations (Document Number)

RoHS Information:	1SND230491F0206
--------------------------	-----------------

Classifications

Object Classification Code:	X
------------------------------------	---

