

CARDMASTER PC 17/16-C3



Sample photo

Order symbol: PC 17/16-C3
Product nbr: 7520080
Description: Enclosure, PC
Remarks: Without main cover

EAN: 6418074010179
El. number:
 Finland: 3422926
 Denmark: 8212016606
 Italy: 7719000

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		166	160	108	Ingress Protection (EN 60529): IP 65
inch:		6.5	6.3	4.3	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			Electrical insulation: Totally insulated
Base colour:		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
Gasket material:		EPDM			UV resistance: UL 508
					Flammability Rating (UL 746 C 5): UL 746C 5V
					Glow Wire Test (IEC 695-2-1) °C: 960
					NEMA Class: NEMA 1, 3, 3R, 12, 13
Temperatures:					
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MP 17/16		Mounting plate			Underwriters Laboratories
FP 17/16		Front plate (aluminium)			Fimko
FC PC 17/16		Frame of PC front plate			Europe EN 62208: 2003
					UL Canada
					Gost R

