

## Cable tie - WT-HF 12,6X850 - 3240730

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable binders for quick and secure bundling, standard version

### Key commercial data

Packing unit	1 PCE
Minimum order quantity	50 PCE
GTIN	 4 046356 704465
Custom tariff number	39269097
Country of origin	CROATIA

### Technical data

#### Dimensions

Length (b)	850 mm
Width (a)	12.6 mm

#### General

Color	transparent
Type	Internal teeth
Inflammability class according to UL 94	V2
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Short-term temperature	110 °C

# Cable tie - WT-HF 12,6X850 - 3240730

## Technical data

### General

Components	free from silicone and halogen
Material	PA 6.6

## Classifications

### ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

### UNSPSC

UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703
UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703

### eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702

## Approvals

### Approvals

---

#### Approvals

UL Recognized / LR / GL / BV / DNV / RINA

---

#### Ex Approvals

---


#### Approvals submitted

---

## Cable tie - WT-HF 12,6X850 - 3240730

### Approvals

#### Approval details

UL Recognized 

LR

GL

BV

DNV

RINA

### Accessories

#### Accessories

Cable tie tool - UNIFOX-CT 4,8 - 1212475



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Cable tie tool - UNIFOX-CT 4,8P - 1212609



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm