

## Datasheet

Art.No. 80.020.4103.0

Solid state relay FLARE-230VAC/48VDC-0,5A

flare, solid state relay with 6,2 mm overall width, input, transistor module, spring clamp terminal, input: 230 V AC, output: 4,5 -53 V DC/0,5 A, with jumper At the in-/output, type: flare-230VAC/48VDC-0,5A



|            |               |
|------------|---------------|
| Art.No.    | 80.020.4103.0 |
| EAN        | 4015573438866 |
| Order unit | 10 pieces     |

## Approvals



## Technical data

### General

|                 |    |
|-----------------|----|
| Modular version | No |
|-----------------|----|

### Technical data

|                            |                          |
|----------------------------|--------------------------|
| Connection type            | Tension clamp connection |
| Type of excitation         |                          |
| Min. connection voltage    | 4.4 V                    |
| Max. connection voltage    | 53 V                     |
| Rated operating current DC | 0.5 A                    |
| Min. control voltage       | 90 V                     |
| Max. control voltage       | 250 V                    |

### Dimensions

|        |        |
|--------|--------|
| Depth  | 70 mm  |
| Width  | 6.2 mm |
| Height | 89 mm  |

### Classification

|            |                             |
|------------|-----------------------------|
| ECLASS 8.1 | 27371014: Solid state relay |
| ETIM 5.0   | EC002055: Solid state relay |
| ETIM 4.0   | EC002055: Solid state relay |
| ETIM 3.0   | EC002055: Solid state relay |



Drawings

