

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [90327-3318](#)
Status: **Active**
Overview: [Picoflex® Connectors](#)
Description: Picoflex® PF-50, Low Profile, IDT Receptacle, 18 Circuits, White, Palladium Nickel with Gold (Au) Flash Plated, Reeling Option A

Documents:

[3D Model](#) [Packaging Specification PK-90327-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0011 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179


General

Product Family Ribbon Cable / Wire Trap Connectors
 Series [90327](#)
 Comments Low Profile|Reeling Option A
 Component Type Housing
 Glow-Wire Compliant No
 Overview [Picoflex® Connectors](#)
 Product Name Picoflex®
 UPC 800753669499

Physical

Circuits (Loaded) 18
 Circuits (maximum) 18
 Color - Resin White
 Durability (mating cycles max) 100
 Entry Angle Vertical
 Flammability 94V-0
 Lock to Mating Part Yes
 Material - Metal Phosphor Bronze
 Material - Plating Mating Palladium Nickel
 Material - Plating Termination Gold
 Material - Resin Polyester
 Net Weight 2.737/g
 Number of Rows 2
 PCB Locator No
 PCB Retention None
 Packaging Type Bag
 Pitch - Mating Interface 1.27mm
 Pitch - Termination Interface 1.27mm
 Polarized to Mating Part Yes
 Polarized to PCB No
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) N/A
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style IDT or Pierce
 Wire Insulation Diameter 1.00mm max.
 Wire Size AWG 26, 28
 Wire/Cable Type Ribbon Cable

Electrical



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[90327Series](#)

Mates With

Low Profile Vertical [90325](#) , Low Profile Right Angle [90800](#) , [90715](#) , [90814](#) , [90779](#)
 Vertical, [91714](#) 1.27mm Pitch Picoflex® PF-50 Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool (Plastic) for 4-26 Circuit	0690081070
Arbor Press Fixture	0690201902
Extractor Tool for Connectors	0621006000

Current - Maximum per Contact
Voltage - Maximum

1.2A
250V

Material Info

Reference - Drawing Numbers

Packaging Specification
Product Specification

PK-90327-001
PS-99020-0011

Handtool for 0690081090
Connectors, 4-26
Circuit
Arbor Press Fixture 0690201908
Semi-Automatic 0691271001
Bench Press PB14
for 4-26 Circuit
Semi-Automatic 0691271004
PB14 Bench Press
with Auto De-reeling
Assembly of De- 0691275045
Tape Unit for
PB14 Part Number
069127-1001

This document was generated on 01/14/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION