

Datasheet

RS Pro Non-Fused Terminal Block, Screw Down Terminals, PE, 400 V

RS Stock No: **867-0975**



Product Details

RS Pro non-fused terminal block in natural colour, is made of polyethylene with brass inserts and galvanised steel screws. This terminal block with 12 ways, features screw down termination. The cable mount block has a voltage rating of 400 V and 30 to 76 A current rating.

Features and Benefits

- Temperature rating of +80°C
- Easy cut
- Made of polyethylene



ENGLISH

Specifications:

Contact Material	Brass
Current Rating	30 to 76 A
Material	PE Housing
Maximum Operating Temperature	+80°C
Mounting Type	Cable Mount
Number of Ways	12
Termination Method	Screw Down
Voltage Rating	400 V
Wire Size	16 mm ²
Colour	Natural
Dimensions	165 x 25.5 x 19.8 mm
Standards Met	RoHS, CE