

IDXPERT™ Handheld Labeler

www.BradyID.com/idxpert

Sign And Label Printers



More Types of Labels

- Colored continuous tapes for equipment ID and safety warnings
- PermaSleeve™ Wire Marker Sleeves
- Self-Laminating wire & cable markers
- Terminal Block and patch panel markers
- Face Plate & Outlet markers
- General-purpose industrial die-cut labels

More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

More Symbols

- Code 39 and 128 bar codes
- 82 Symbols including electrical, voice/data, safety & protection, warning, and machine & operational

More Brains

- Drop Lock & Go™ Smart Cartridges™
- Pre-calibrated to orient the label correctly
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

Prints Clean & Fast

- Users of dot-matrix printers will benefit from crisp, non-smearing thermal transfer print quality, faster print speed and more text-editing and symbols capabilities

Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need
- Runs on 6 AAs or optional AC power supply



Catalog No.	Description
XPRT-ABC	Printer* (ABC Layout)
XPRT-HC-ABC	Hard Case for ABC Layout
XPRT-KEY	Printer* (KEYBOARD Layout)
XPRT-CONT	Continuous Only Printer
XPRT-HC-KEY	Hard Case for KEYBOARD Layout
XPRT-AC	AC Adapter
LABXPRT-SER-USB	Serial-to-USB adapter for PC cable
PCCABLE-1	Spare PC Cable for Upgrades Only
PCK-4	Cleaning Kit
LM5STDE	LabelMark™5 Software (single user)
XPRT-ABC-KIT-LM	Printer* (ABC Layout) and LabelMark™5 Standard Software Kit
XPRT-KEY-KIT-LM	Printer* (Keyboard Layout) and LabelMark™5 Standard Software Kit

* Printer ships with: Hard Case, 1.5" Continuous Sample Roll Tape, PC cable, Product CD

Indoor/Outdoor Grade Facility & Safety Labels

This indoor/5 year outdoor vinyl is very pliable and conforms well to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins and equipment. Excellent resistance to oils, detergents, dirt, grime and many solvents.

- B-580 Indoor/Outdoor Vinyl material
- Permanent adhesive, good for rough surfaces
- Temp Range -40°F to 248°F (-40C to 120C)

Note: As of February 2011, B-580 material will be replaced with B-595 material. When ordering after this date, please replace "580" with "595" in the part number.

For example: part number "XC-750-580-WT-BK" would become "XC-750-595-WT-BK"

Diagram




Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color
			A	B	A	B	
⊙	XC-375-499	1 roll (cont.)	20 ft.	0.375	9.14m	9.525mm	BK on WT
⊙	XC-500-499	1 roll (cont.)	20 ft.	0.500	9.14m	12.700mm	BK on WT
⊙	XC-750-499	1 roll (cont.)	20 ft.	0.750	9.14m	19.050mm	BK on WT
⊙	XC-1000-499	1 roll (cont.)	20 ft.	1.000	9.14m	24.400mm	BK on WT
⊙	XC-750-580-WT-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on WT
⊙	XC-750-580-OR-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on O
⊙	XC-750-580-YL-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on YL
⊙	XC-750-580-CL-BK	1 roll (cont.)	25 ft.	0.750	9.14m	19.050mm	BK on CL
⊙	XC-750-580-WT-RD	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on RD
⊙	XC-750-580-GN-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on GN
⊙	XC-750-580-BL-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on BL
⊙	XC-750-580-RD-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	RD on WT
⊙	XC-500-580-WT-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on WT
⊙	XC-1000-580-WT-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on WT
⊙	XC-1500-580-WT-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on WT
⊙	XC-500-580-OR-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on OR
⊙	XC-1000-580-OR-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on OR
⊙	XC-1500-580-OR-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on OR
⊙	XC-500-580-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on YL
⊙	XC-1000-580-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on YL
⊙	XC-1500-580-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on YL
⊙	XC-500-580-CL-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on CL
⊙	XC-1000-580-CL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on CL
⊙	XC-1500-580-CL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on CL
⊙	XC-500-580-RD-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on RD
⊙	XC-1000-580-RD-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on RD
⊙	XC-1500-580-RD-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on RD
⊙	XC-500-580-GN-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on GN
⊙	XC-1000-580-GN-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on GN
⊙	XC-1500-580-GN-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on GN
⊙	XC-500-580-BL-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on BL
⊙	XC-1000-580-BL-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on BL
⊙	XC-1500-580-BL-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on BL
⊙	XC-500-580-WT-RD	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	RD on WT
⊙	XC-1000-580-WT-RD	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	RD on WT
⊙	XC-1500-580-WT-RD	1 roll (cont.)	30 ft.	1.500	9.14m	38.10m	RD on WT