

Datasheet

Item No. 96.232.1030.1

Cable assembly RST20I3K1BS 15 10SW

Extension cable, female - male, length 1m, RST20i3, 3 pole, 250V/20A, cable type H07RN-F, cross section 1,5 mm², color of coding: black



Item No.	96.232.1030.1
EAN	4015573761544
order unit	50 Piece(s)

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP66/IP68
Cable type	H07RN-F
Cable colour	Black
Cable diameter	9.8 mm
Version of cable	Female - male

Material

Surface finish	Silver-plated
Halogen free	No
Continuous temperature of cable	60 °C
Insulation components continuous temperature	100 °C

Dimensions

