








- 注記:
- △ 相手ハウジングと所定の機能を満たしてかん合できること。
 - △ フードの反りは0.2以内。
 - 3 プリント基板への取付けは JIS B1115 M3 1種のタッピンネジで締め付けた後はんだ付けする。
 - 4 適用製品規格; 108-5093
 - △ -A- 面より2mmの範囲で測定のこと。
 - 6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。
 - △ 金めっき位置番号: 下図参照のこと。

- NOTE:
- △ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
 - △ WARPAGE 0.2 MAX.
 - 3 SOLDERING AFTER MOUNTING P.C. BOARD BY 3mmDIA TAPPING SCREW, SPECIFIED IN JIS B1115
 - 4 PRODUCT SPEC NO. 108-5093
 - △ TO BE MEASURED WITHIN 2mm FROM -A-
 - 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX. WITHOUT RECEPTACLE CONTACT
 - △ GOLD PLATED POSITION NUMBER.



プリント基板取付寸法図
(MOUNTING DIMENSIONS FOR P.C. BOARD)

1. 板厚, 1.6±0.15
(P.C.B. THICKNESS, 1.6±0.15)
2. 公差, ±0.1
(TOLERANCE, ±0.1)



	1～11	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	2-5172038-1
OBSOLETE	6～11	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	YELLOW	3-172038-7
		PRE-TIN			
OBSOLETE	1～11	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	GREEN	2-172038-4
	1～11	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	2-172038-1
OBSOLETE	1～11	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	GREEN	1-172038-4
OBSOLETE	1～11	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	1-172038-1
OBSOLETE		PRE-TIN		YELLOW	172038-7
OBSOLETE		PRE-TIN		GRAY	172038-6
OBSOLETE		PRE-TIN		BLUE	172038-5
		PRE-TIN		GREEN	172038-4
OBSOLETE		PRE-TIN		BROWN	172038-3
OBSOLETE		PRE-TIN		BLACK	172038-2
		PRE-TIN		NATURAL	172038-1
GOLD PL. POSITION No. 金めっき位置番号		SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
		CONTACT FINISH コンタクト仕上			

TOLERANCE UNLESS OTHERWISE SPECIFIED:
一般公差
0<X≤10: ±0.2
10<X≤30: ±0.25
30<X≤100: ±0.3
ANGLE: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 特
mm

MATERIAL
材料
HSG: 66 NYLON
CONTACT: BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH 仕上
SEE TABLE

DWN
CHK
APVD
PRODUCT SPEC
APPLICATION SPEC

T.SHINOHARA
K.BETSUI
K.BETSUI
SEE NOTE 4
—

WEIGHT
—

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称
11P HORIZONTAL TYPE CAP HOUSING
MULTI-INTERLOCK CONN.
WIRE TO PCB

SIZE
A2

CAGE CODE
00779

DRAWING NO
番号
172038

RESTRICTED TO
—

SCALE
尺度
2:1

SHEET
1 of 1

REV
G3

AMP 1471-9 REV 31MAR2000