



NO	DESCRIPTION	DATE
①	WORKING VOLTAGE → VOLTAGE RATING DEL PROOF VOLTAGE	09.10.15'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-4 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 VOLTAGE RATING: 500 VOLTS MAX. 

2.0 MATERIALS


- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
2.4 CRIMP FERRULE: BRASS PER JIS-C3604

3.0 FINISHES AND OTHERS



- 3.1 SEE BELOW TABLE FOR DETAILS.**

4.0 MECHANICAL

- 4.1 FOR USE WITH RG174U OR SIMILAR STYLE CABLE
4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER/CRIMP
4.3 CRIMP SIZE REQUIRED: CONTACT: 1.8(.071) HEX. CRIMP TOOL
FERRULE: 3.5(.138) HEX. CRIMP TOOL
5.5(.216) HEX. CRIMP TOOL



STRIPPING DIMENSION
SCALE 2:1



5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C**

10	INSULATION II	TEFLON	1	NONE
9	SHELL	BRASS	1	SILVER 70 μ " MIN.
8	GASKET	SILICONE	1	RED
7	WASHER II	BRASS	1	NICKEL
6	SPRING WASHER	SK-5	1	NICKEL
5	WASHER I	BRASS	1	SILVER 70 μ " MIN.
4	BODY	BRASS	1	SILVER 70 μ " MIN.
3	CENTER CONTACT	BRASS	1	SILVER 70 μ " MIN.
2	CRIMP FERRULE	BRASS	1	SILVER 70 μ " MIN.
1	INSULATION I	POM	1	NONE
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by DATE:



DESCRIPTION		BNC STRAIGHT PLUG CRIMP									
製圖	DRAWN	TOLERANCE		品名	13-55-1 T.S.S 58U TO 174U			日期	DATE	版次	REV.
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT (50Ω)			日期	11.25.92'	版次	B-1
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	13-0260				
	Arc				mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
	Jenny				ANGLE						