

Datasheet

## RS Pro Maximum of 5 V ac 75dB sound SMD Square Wave External Piezo Buzzer

RS Stock No: **754-1977**



### Product Details

RS Pro external piezo buzzer operates at voltages up to 5 V ac. This square wave buzzer delivers 75 dB sound at frequencies up to 520 Hz. It is suitable for applications that require high sound output.

### Features and Benefits

- Round cased SMT Piezo transducers
- High sound output
- Requires external drive circuits to operate

**Specifications:**

Drive Type	External
Mounting Type	Surface Mount
Tone Type	Square Wave
Diameter	10 mm
Dimensions	10 (dia.) x 3.1 mm
Height	3.1 mm
Maximum Frequency	520 Hz
Maximum Operating Temperature	+70°C
Maximum Supply Voltage	5 V ac
Minimum Operating Temperature	-20°C
Minimum Supply Voltage	25 V ac
Sound Level	75 dB
Supply Current	5 mA