

EK EKPE 180 T



Sample photo

Order symbol: EKPE 180 T
Product nbr: 2538146
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074013866
EI. number:
 Finland: 3425472
 Electric No. Italy: 7502145
 Electric No. Sweden: 2538146

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	380	280	180	EKPG Base, PC
inch:	15.0	11.0	7.1	EKP 30-G Cover

Materials:

Material: Polycarbonate

Base colour: RAL 7035 -light grey

Cover screws material: Polyamide

Cover colour: Clear transparent

Cover screws colour: Grey

Gasket material: Polyurethane

EKP 80-G	Cover
EKP 30-T	Cover
EKP 80-T	Cover
EKPVT	Mounting plate
EKPXT	Mounting plate isolated
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail
EKPZR	Extension frame

Temperatures:

Temperature °C (short term): -40 ... 120 °C

Temperature °C (continuous): -40 ... 80 °C

Temperature °F (short term): -40 ... 250 °F

Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP66/IP67

Impact Resistance (EN 62262): IK08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C: 960

NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Accessories:

EKPE Base, PC

Certificates:

SGS Fimko

Gost R

