

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		B	REV PER ECO 08-009474	7/22/2008	DW	JL

- 1

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:NATURAL
- 2

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:BLACK
- 3

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4

ZINC PER QQ-Z-363.
- 5

BERYLLIUM COPPER PER QQ-C-530.
- 6



BRASS PER ASTM-B-453.
- 7

NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
- 8


TIN PLATE PER ASTM-B-545
3.81 μm [.000150] MINIMUM THICK.
- 9

GOLD PLATE PER ASTM-B-488
0.76 μm [.000030] MINIMUM THICK.
10.

SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

	5413194-2
	5413194-1
HOUSING MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 21APR2005	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK J. HAVENER - 21APR2005		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. LIPPERT - 21APR2005	NAME	
		PRODUCT SPEC	JACK, RIGHT ANGLE, PCB, 75 OHM, BNC	
	0. PLC ± - 1. PLC ± - 2. PLC ± 0.06 [.002] 3. PLC ± - 4. PLC ± - ANGLES ± -	APPLICATION SPEC		
		WEIGHT	SIZE CAGE CODE DRAWING NO	
MATERIAL SEE NOTES 1-6		FINISH SEE NOTES 7-9		
CUSTOMER DRAWING		RESTRICTED TO		
			A1 00779 C=5413194	
		SCALE 4:1	SHEET 1 OF 1	REV B