


KEMET Part Number: ALS30A152KF400
(A331LM152M400A)

ALS30, Aluminum Electrolytic, 1,500 uF, 20%, 400 VDC, -40/+85°C



Dimensions

D	51mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Packaging Specifications

Weight:	300 g
Sleeving:	Yes
Packaging:	Bulk, Box

General Information

Supplier:	KEMET
Series:	ALS30
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M12x16. Mounting Clip (Sold Separately): V4/UTE2737
Shelf Life:	156 Weeks

Specifications

Capacitance:	1,500 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage At 85C)
Resistance:	92 mOhms (100Hz 20C), 65 mOhms (10kHz 20C)
Ripple Current:	7.8 Amps (100Hz 85C), 13.1 Amps (10kHz 85C)
Leakage Current:	3600 uA (5min 20°C)