



### Main

Range of product	Altira
Product or component type	Switch
Device presentation	Mechanism
Cover plate colour tint	Polar white (RAL 9003)

### Complementary

Wiring device mounting	Flush Surface
Product destination	OptiLine 45 installation system Fixing frame
Switch function	2-way switch
Rated current	16 A - 250 V AC
Actuator	Rocker
Number of modules	2 modules
Fixing mode	Clip-in
Connections - terminals	3 x screwless terminals
Number of cables	2 x 1.5...2.5 mm <sup>2</sup> for solid stranded cable(s) 2 x 1.5...2.5 mm <sup>2</sup> for rigid cable(s)
Material	PC for mechanism cover
Surface treatment	Untreated
Surface finish	Satin
Embedding depth	21 mm
Height	45 mm
Width	45 mm
Depth	28 mm
Product weight	0.028 kg

### Environment

Standards	IEC EN 60669-1
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-15...60 °C
IK degree of protection	IK04
IP degree of protection	IP21 D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H <sub>2</sub> O <sub>2</sub> )
Environmental health and issues	Halogen free