

## **PRODUCT SPECIFICATION – RS COMPONENTS**

**PRODUCT CODE:** PF75ISRS

**PRODUCT DESCRIPTION:** Braided Hose Metal Push Fit inc VALVE 15mm x 1/2" x 30cm

**RS CODE:** 7845314

### **1) MATERIAL / APPEARANCE**

*metal part : CW617N sleeve : H62 finish: Nickel plated hose: rubber*

### **2) PRODUCT DIMENSIONS**

*L = 127mm, W = 356mm, H = 35mm & 0.1845 Kg*

### **3) INSTALLATION INSTRUCTIONS AND DETAILS**

- 1. Turn off the water supply, dismantle the old hose.*
- 2. The perfect installation of a braided hose is vertical. Connect the nut side of the hose to the infall of the water supply , screw the nut tightly by hand first, then twist 1/4 circle by spanner to reinforce.*
- 3. Connect the push fit side to the connection-peg. It's better that the braided hose keep slack situation after installation.*

### **4) PACKAGING**

*LDPE Bag & Paper Label*

### **5) OUTLINE OF PRODUCTION METHOD**

*metal parts: forging*

### **6) PRODUCT RATING**

### **7) APPROVALS**

*WRAS*