

Datasheet

Zinc Plated Toggle Latch, Spring Loaded, 75kgf Op. Tension

RS Stock number [197-4097](#)



Description:

A robust fully adjustable safety lock design with the possibility of sealing. Adjustment is made by a screw slide hidden in the body of the latch and further automatic adjustment is made by compression springs in the latch arms. Normal operating tension is 55kgf maximum operating tension is 75kgf. Suitable for use on heavy duty containers. Suitable for screw fixing using 5xM5 screws for catch and latch.

Features:

- Dimensions 185 x 50 x 18mm
- Finish Zinc Plated
- Lockable Yes, Lock Not Included
- Material Steel
- Operating Tension 75kgf
- Spring Loaded Yes