

Extra Heavy-Duty Hospital Grade LED Illuminated Face Receptacles, Back & Side Wire, 15A, 125V, White

8200ILW



Extra Heavy-Duty Hospital Grade LED
Illuminated Face Duplex Receptacle Back &
Side Wire 15amp 125volt White



features & benefits

- One-piece nickel-plated brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 - #10 AWG stranded or solid copper-clad conductors.
- Auto-ground clip assures positive ground.
- Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: white
Type: Receptacles
Duty: Extra Heavy Duty
Special Features: LED Illuminated Face,back,side wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: .900"
Height U S: 3.281"
Width U S: 1.625"

Technical Information

Amps: 15 Amp
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant