

## Datasheet

**RS Pro Zinc Plated Steel Adjustable Height Mount 140mm  
Rubber 115mm 60mm 169mm 2000kg 120mm M16 3.5°  
RS Stock No: 283-1812**



## Product Details

RS Pro adjustable height mount is a zinc plated steel machine mount, which is suitable for use in less demanding environments. It is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. It has a thread size of M16 and diameter of 140 mm. The foot material of mount is made from rubber and has an adjustable height from 60 to 115 mm. It has a static load capacity of 2000 kg and a thread length of 120 mm with a tilt angle of 3.5°.

## Features and Benefits

- Long bolt offers height adjustment
- Compensates with up to 7° swivel
- For use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery
- Built in levelling bolt means the stainless steel mounts can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability



**Specifications:**

Base Material	Zinc Plated Steel
Diameter	140 mm
Foot Material	Rubber
Maximum Adjustment Height	115 mm
Minimum Adjustment Height	60 mm
Overall Height	169 mm
Static Load Capacity	2000 kg
Thread Length	120 mm
Thread Size	M16
Tilt Angle	3.5°