



# Datasheet

ENGLISH

## SOCKET OUTLET 6P+E IP67 16A 6h






### TechData

Rated current	16A
Commercial series	OPTIMA-SEVEN Series
Poles	6P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	50Hz
Working frequency	60Hz
Colour	RED
Syntetical description	SOCKET OUTLET
Protection degree	IP66/IP67
Types of available outlets	ANGLED

### Approvals and Certifications

**CE** CE Declaration of conformity

### Standards and Laws

-  EN 60309-1 (1999) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

### Packaging

Description	Box
Quantity	5
Gross weight	1.675 KG
Volume	8436 CCM
Dimensions	185x285x160 (MM)