

QUICK CAB PCQ 403017 T



Sample photo

Order symbol:	CAB PCQ 403017 T
Product nbr:	8113058
Description:	Cabinet, PC
Remarks:	Smoked transparent cover

EAN: 6418074011091
El. number:
 Finland: 3421924
 Electric No. Italy: 7682040
 Electric No. Sweden: 2539192

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:	Length	Width	Height
mm:	400	300	170
inch:	15.7	11.8	6.7

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Smoked grey
Cover screws colour:	RAL 5023
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

EKIV 43 Mounting plate

Accessories:

EKIV 27	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set
PAT 12040	Hinge set

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

- Germanischer Lloyd (GL)
- SGS Fimko
- Lloyds Register of Shipping (LR)
- Gost R

QUICK 400x300x170-230

