



Sample photo

Order symbol: ABS 150/125 LT
Product nbr: 6082917
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074052308
El. number:
Finland: 3435244
Denmark: 8212023741
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm: 180	130	125		Ingress Protection (EN 60529): IP 66/67
inch: 7.1	5.1	4.9		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	Smoked grey			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:	Polyamide			NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour:	Black			
Gasket material:	TPE			
Temperatures:				Certificates:
Short term:	-40 ... 80 °C			Fimko
Continuous:	-40 ... 60 °C			Europe EN 62208: 2003
Short term:	-40 ... 175 °F			Gost R
Continuous:	-40 ... 140 °F			
Accessories:				
MIV 150	Mounting plate (Galvanized steel)			
MIN 10	DIN-15 Mounting rail			
MIN 15	DIN-15 Mounting rail			
MIV 10	DIN-35 Mounting rail			
MIV 15	DIN-35 Mounting rail			
FP A 150/180	Front plate (Aluminium)			
HFP 180	Front plate hinge series (2 pcs)			
FP 22046	Wall fastening lug (4 pcs)			

