

CLAMP METERS

AC/DC Digital Clamp Meter, from 0 to 2000A(TRUE RMS)

NEW



CE

MODEL 2009A

- Tear drop shaped jaws for ease of use in crowded cable areas and other tight places.
- Accurate true RMS readings of AC current and voltage regardless of the wave form.
- AVERAGE function to allow for easy reading of fluctuating current or voltage.

● Specifications

AC A	400/2000A
AC V	40/400/750V
DC A	400/2000A
DC V	40/400/1000V
Ω	400/4000Ω
Continuity	400Ω
Frequency	10~4000Hz
Output Voltage	400/2000A DC400mV/200mV
Conductor Size	∅55mm max.

Safety Standard	IEC61010-1 CAT. III 600V IEC61010-1 CAT. II 1000V IEC61010-2-031, IEC61010-2-032
Power Source	6F22(9V)×1 Approx. 15 hours in continuous use
Dimensions	250(L)×105(W)×49(D)mm
Weight	540g approx.
