

Data sheet

TWINAX STRAIGHT BULKHEAD JACK RECEPTACLE

RS stock No: 6563793

6.0(236) MAX. PANEL

3/4"-20UNEF

18.0(709)

2.0(079)

34.1±0.3(1.343±.012)

39±(1.535±.039)

FLAT 17.8(701)

3/4"-20UNEF REF.

∅24(945)

10(394) REF.

∅29(1142) REF.

∅27(1063) REF.

22.0(866) HEX.

3/4"-20UNEF

(130)

3.3

(.709)

(.744)

∅18.9 MIN.

18.0 MIN.

MOUNTING HOLE

APPROVED by _____ DATE: _____

DESCRIPTION		TWINAX STRAIGHT BULKHEAD JACK RECEPTACLE	
8	PILLAR	BRASS	1 NICKEL 100 μ" MIN.
7	INSULATION II	PBT	1 NONE
6	BODY	BRASS	1 NICKEL 100 μ" MIN.
5	CENTER CONTACT	BERYLLIUM COPPER	2 SILVER 70 μ" MIN.
4	INSULATION I	PBT	1 NONE
3	GROUNDING TAG	BRASS	1 NICKEL
2	WASHER	BRASS	1 NICKEL
1	NUT	BRASS	1 NICKEL 100 μ" MIN.
NO DESCRIPTION		MATERIAL	Q'TY FINISH

DRAWN	TOLERANCE	品名	21-04	PBT.S.N	日	DATE	版	REV.
Kristina	±0.2	TITLE	NRHS COMPLIANT		期	05.21.15'	次	A-0
CHECK	XX	UNIT	mm					
APPROVAL	XXX	比例	SCALE					
Jenny	ANGLE ±5°	例	3:1					

1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-200 MHz

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604

2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B186 UNS C17300

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

