

Datasheet

Stainless Steel Toggle Latch

RS Stock number [197-4176](#)



Description:

A robust, general purpose latch with a 4mm wire link and the facility to padlock secure. Normal latch to catch fixing centre is 63.3mm (max.) giving a 70kgf max operating tension. Suitable for screw fixing using 2xM4 screws for latch and 2xM5 screws for catch.

Specifications:

| | |
|--------------------|-----------------|
| Depth: | 17 mm |
| Length: | 84 mm |
| Material: | Stainless Steel |
| Operating Tension: | 70 kgf |
| Width: | 32 mm |

Dimensional Drawing:

