

156-00856

Article Number: 156-00856

Cable Tie and Edge Clip, 30lb, 6.0" Long, EC4B, Panel Thickness 0.04" - 0.12", PA66HS, Black, 500/bag



Download drawing



Download spec sheet

Base Data

Local Order Number 156-00856

Type T30REC4B

Color Black (BK)

- Features and Benefits**
- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
 - Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
 - Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

Product Description The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Fixation Method (FF) EdgeClip, top, assembled, 2 piece

Identification Plate Position none

Releasable Closure (Yes/No) No

Variant Inside Serrated

Short Description Cable Tie and Edge Clip, 30lb, 6.0" Long, EC4B, Panel Thickness 0.04" - 0.12", PA66HS, Black, 500/bag

Product Dimensions

Minimum Tensile Strength (imperial) 30.0 lbs

Minimum Tensile Strength (N) 135 N

Length L (imperial) 6.0 "

Length L (metric) 150.0 mm

Length L2 (imperial) 0.6 "

Length L2 (metric) 14.0 mm

Width W (imperial) 0.14 "

Width W (metric) 3.6 mm

Width W2 (imperial) 0.5 "

Width W2 (metric) 11.5 mm

Height H (imperial) 0.05 "

Height H (metric) 1.3 mm

Height H2 (imperial) 0.4 "

Height H2 (metric) 10.8 mm

Bundle Diameter min (imperial) 0.06 "

Bundle Diameter min (metric) 1.5 mm

Bundle Diameter max (imperial) 1.3 "

Bundle Diameter max (metric) 32.0 mm

| | |
|--|---------|
| Panel Thickness max. (imperial) | 0.12 " |
| Panel Thickness max. (metric) | 3.00 mm |
| Panel Thickness min. (imperial) | 0.04 " |
| Panel Thickness min. (metric) | 1.00 mm |
| Thickness T (imperial) | 0.043 " |
| Thickness T (Metric) | 1.1 mm |

Logistics and Packaging

| | |
|-------------------------|--------|
| Quantity per | bag |
| Package Quantity | 500 |
| Weight (Metric) | 4.5 kg |

Material and Specifications

| | |
|------------------------------|---|
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut | PA66HS |
| Material Cable Tie | Polyamide 6.6 heat stabilized (PA66HS) |
| Material Edge Clip | Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) |
| Flammability | UL94 HB |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| ROHS Conformity | Yes |