

## Reflector

BLOWN REFL 63MM 40W 240V P

0015550



### Range features

- Blown glass reflector lamps
- Pearl crown and integral aluminium reflector
- Available in 6 diameters
- Ideal for accent lighting in commercial and domestic applications
- Suitable for shop windows, displays, discos and clubs as well as in the home
- For use in track or surface mounted spotlights or in recessed downlights



### PRODUCT OVERVIEW

Light colour	825 Homelight
Technology	Incandescent
Ordering number	0015550
Average life (Rated) (h)	1000
Lamp shape	Reflector
Lamp finish	Aluminium
Dimmable	yes
Cap/Base	E27
Type	Standard Reflector
EAN code	5410288155500
CRI (Ra)	100
Beam angle(°)	35
Colour temperature (K)	2500
Watt (Nominal) (W)	40
Voltage (V)	240

# Reflector

*BLOWN REFL 63MM 40W 240V P*

**0015550**

## DATA TABLE

### General data

<b>Ordering number</b>	0015550
<b>Technology</b>	Incandescent
<b>Average life (Nominal) (h)</b>	1000
<b>Average life (Rated) (h)</b>	1000
<b>Energy saving lamp</b>	No
<b>Lamp finish</b>	Aluminium
<b>Lamp shape</b>	Reflector
<b>Dimmable</b>	yes
<b>Cap/Base</b>	E27
<b>Type</b>	Standard Reflector
<b>EAN code</b>	5410288155500
<b>E-number FI</b>	4747311
<b>E-number SE</b>	8355253
<b>Long description</b>	Blown glass reflector lamps. Pearl crown and integral aluminium reflector. Available in 6 diameters. Ideal for accent lighting in commercial and domestic applications. Suitable for shop windows, displays, discos and clubs as well as in the home. For use in track or surface mounted spotlights or in recessed downlights
<b>Product name</b>	BLOWN REFL 63MM 40W 240V P
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	instant full light
<b>Warm-up time to 60% of full light (max) (s)</b>	Instant full light
<b>Fixture rating</b>	Open
<b>IEC Reference</b>	IEC 60064
<b>IEC Reference 2</b>	IEC 60432
<b>Intended purpose</b>	General lighting
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	10
<b>Optimal operating condition (°C)</b>	25

### Optical data

<b>Light colour</b>	825 Homelight
<b>CRI (Ra)</b>	100
<b>Beam angle(°)</b>	35
<b>Colour temperature (K)</b>	2500
<b>Peak intensity (cd)</b>	325

# Reflector

*BLOWN REFL 63MM 40W 240V P*

**0015550**

## Electrical data

<b>kWh per 1000 hours burning time</b>	40
<b>Watt (Rated) (W)</b>	40
<b>Watt (Nominal) (W)</b>	40
<b>Voltage (V)</b>	240
<b>Current (A)</b>	0.167
<b>Lamp power factor</b>	1

## Physical data

<b>Lamp Length (mm) - C/L</b>	104.5
<b>Lamp Diameter (mm) - D</b>	63
<b>Packaging outer width (cm)</b>	33
<b>Packaging outer length (cm)</b>	57
<b>Packaging outer height (cm)</b>	27
<b>Packaging single width (cm)</b>	6.1
<b>Packaging single length (cm)</b>	6.1
<b>Packaging single height (cm)</b>	10.4

## Reflector

*BLOWN REFL 63MM 40W 240V P*

**0015550**

### TECHNICAL DRAWINGS

---

