

88 06 250

KNIPEX Alligator® Water Pump Pliers



- more output and comfort compared to conventional water pump pliers of the same length: 9-notch adjustment positioning for 30 % more gripping capacity
- good access to the workpiece due to slim size of head and joint area
- self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- box-joint design: high stability due to double guide
- guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, oil-hardened

Article No.	88 06 250
EAN	4003773039303
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Head	
Insulation standard	IEC 60900 DIN EN 60900
Adjustment positions	9
Capacities for pipes Ø Inch	2
Capacities for nuts mm	46
Capacities for pipes Ø mm	50
Length mm	250
Net weight g	374



technical change and errors excepted



Spare Parts

Article No.	EAN	
88 09 250	4003773053514	Bolt (Kerpin) for 88 250