

SES-QUICK cable ties SL

for general use

PA 6.6 natural - black






















SES-QUICK

-40 to +85°C



• SL cable ties with inside serrations

type		article number		dimensions length x width mm	maximum bundle Ø mm	tensile strength daN	
		natural (NL)	black (BK)				
85/24	SL-M*	0186 0010 018	0186 0960 010	85 x 2,4	16	8	1 000
85/24	SL-C	0186 0011 018	0186 0975 010	85 x 2,4	16	8	100 
100/25	SL-M*	0186 0020 018	0186 0961 010	100 x 2,5	20	8	1 000
100/25	SL-C	0186 0021 018	0186 0976 010	100 x 2,5	20	8	100 
150/26	SL-M*	0186 0022 018	0186 0962 010	150 x 2,6	40	8	1 000
150/26	SL-C	0186 0023 018	0186 0977 010	150 x 2,6	40	8	100 
200/26	SL-M*	0186 0210 018	0186 0963 010	200 x 2,6	50	8	1 000
200/26	SL-C	0186 0610 018	0186 0978 010	200 x 2,6	50	8	100 
145/34	SL-M*	0186 0030 018	0186 0964 010	145 x 3,4	35	13	1 000
145/34	SL-C	0186 0031 018	0186 0979 010	145 x 3,4	35	13	100 
210/34	SL-M	0186 0220 018	0186 0965 010	210 x 3,4	55	13	1 000
210/34	SL-C	0186 0620 018	0186 0980 010	210 x 3,4	55	13	100 
300/36	SL-M	0186 0230 018	0186 0966 010	295 x 3,6	76	13	1 000
300/36	SL-C	0186 0630 018	0186 0981 010	295 x 3,6	76	13	100 
370/36	SL-C	0186 0240 018	0186 0967 010	370 x 3,6	102	13	100 
160/46	SL-M	0186 0250 018	0186 0957 010	160 x 4,6	40	22	1 000
160/46	SL-C	0186 0650 018	0186 0974 010	160 x 4,6	40	22	100 
185/46	SL-M	0186 0040 018	0186 0968 010	185 x 4,6	47	22	1 000
185/46	SL-C	0186 0041 018	0186 0983 010	185 x 4,6	47	22	100 
200/48	SL-M	0186 0046 018	0186 0046 010	200 x 4,8	50	22	1 000
200/48	SL-C	0186 0045 018	0186 0045 010	200 x 4,8	50	22	100 
250/46	SL-M	0186 0540 018	0186 0958 010	250 x 4,6	60	22	1 000
250/46	SL-C	0186 0545 018	0186 0959 010	250 x 4,6	60	22	100 
300/46	SL-M	0186 0235 018	0186 0969 010	300 x 4,6	76	22	1 000
300/46	SL-C	0186 0635 018	0186 0984 010	300 x 4,6	76	22	100 
380/47	SL-C	0186 0050 018	0186 0970 010	380 x 4,7	109	22	100 
180/76	SL-C	0186 0260 018	0186 0987 010	180 x 7,6	47	54	100 
240/76	SL-C	0186 0270 018	0186 0988 010	240 x 7,6	55	54	100 
300/76	SL-C	0186 0280 018	0186 0989 010	300 x 7,6	76	54	100 
365/76	SL-C	0186 0060 018	0186 0971 010	365 x 7,6	100	54	100 
450/76	SL-C	0186 0069 018	0186 0069 010	450 x 7,6	128	54	100
550/90	SL-C	0186 0062 018	0186 0973 010	550 x 8,9	155	79	100
780/90	SL-C	0186 0290 018	0186 0972 010	775 x 8,9	230	79	100
230/130	SL-C	0186 0170 018	0186 0170 010	230 x 13	55	114	100
480/130	SL-C	0186 0171 018	0186 0171 010	480 x 13	120	114	100
580/130	SL-L	0186 0172 018	0186 0172 010	580 x 13	155	114	50
730/130	SL-C	0186 0173 018	0186 0173 010	730 x 13	204	114	100
880/130	SL-L	0186 0174 018	0186 0174 010	880 x 13	248	114	50
1030/130	SL-C	0186 0175 018	0186 0175 010	1030 x 13	295	114	100



* Packed per 10 bundles of 100 pieces.



Bag available with a European suspension hole.