

Datasheet

RS Pro Butt Wire Splice Connector, Red, Insulated, Tin Plated 22 → 16 AWG

RS Stock No: **613-9794**



Product Details

RS Pro butt wire splice connector in red colour, is insulated and tin plated. This 4 mm connector has a wire size of 22 to 16 AWG. It has a range of insulated crimp butt splice terminal made from copper with flared vinyl insulation. This insulated crimp butt splice wire connectors are colour is, coded for use with different wire sizes including mini yellow 0.2 - 0.5 mm².

Features and Benefits

- Insulated crimp butt splice terminals made from copper with flared vinyl or nylon (mini-yellow) insulation
- This insulated crimp butt splice wire connectors are colour coded for use with different wire sizes
- Mini yellow 0.2 - 0.5 mm², red 0.5 - 1.0 mm², blue 1.5 - 2.5 mm² and yellow 2.5 - 6.5 mm²

Specifications:

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Shrouded	Shrouded
Splice Type	Butt
Diameter	4 mm
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	24.2 mm
Wire Size	22 to 16 AWG
Current Rating	9 to 18 A
Temperature Rating	+75°C
Voltage Rating	600 V