




.115-.170	100	LOOSE PIECE, BOX	8-52936-1
.115-.182	5000	-2 ON TAPE	52936-3
.115-.182	1000	LOOSE PIECE	52936-2
.115-.170	5000	-1 ON TAPE	52936-1
.115-.170	1000	LOOSE PIECE	52936
WIRE INSULATION OD	QTY	PACKAGE TYPE	PART NO

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

FOR APPLICATION TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER

1-800-522-6752

TOOLING ASSISTANCE CENTER

1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:

105°C

VOLTAGE RATING:

300 V MAX

CIRCULAR MIL AREA:

1.04-2.62mm² [2,050-5,180]

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

4

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .008

4 PLC ± -

ANGLES ± 5°

FINISH

5

DWN jr ruth 19MAR10

CHK T MICHELUTTI 19MAR10

APVD T MICHELUTTI 19MAR10

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

STE

TE Connectivity

NAME

TERMINAL, SHORT SPRING SPADE, PIDG, WIRE SIZE: 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-52936

SCALE

6:1

SHEET

1 OF 1

REV

K2

1470-19 (3/11)