



ENGLISH

Datasheet

## RS Pro Steel Abrasive Circular Brush, 15000rpm, 50mm Diameter

RS Stock No: **779-251**



### Product Details

RS Pro stainless steel abrasive circular brush has a diameter of 50 mm with a shaft diameter of 6 mm. A circular wire brush is used in power tools. It is perfect for cleaning welds or removing burr from steel enclosures or fittings.

### Features and Benefits

- Suitable for cleaning or finishing hard to reach areas or internal surfaces
- 15000 rpm maximum safe speed
- Stainless steel bristle construction
- Shank fixing type



ENGLISH

### Specifications:

Bristle Material	Steel
Fixing Type	Shank
Bristle Length	13 mm
Diameter	50 mm
Fixing Size	6 mm
Maximum Safe Speed	15000 rpm
Suitable For	Cleaning or Finishing Hard to Reach Areas or Internal Surfaces