




**5PC. FLEX HEAD SET (METRIC)**

PART NO.	CONTENT		G.W.(kg)
09082	5PC.	12	10.7

DESCRIPTION:  
10mm, 11mm, 12mm,  
13mm, 14mm




**7PC. XL LOCKING FLEX HEAD SET (METRIC)**

PART NO.	CONTENT			G.W.(kg)
09043	7PC.	6	12	16.6

DESCRIPTION:  
10mm, 12mm, 13mm, 14mm,  
15mm, 17mm, 19mm



**3PC. SOCKET ADAPTER SET (METRIC)**

PART NO.	CONTENT			G.W.(kg)
09084	3PC.	10	40	6.0



DESCRIPTION:  
1/4"DR.x10MM  
3/8"DR.x13MM  
1/2"DR.x19MM



**New**



**XL X-BEAM® (S.A.E.)**

PART NO.	SIZE	L(mm)	A(mm)			G.W.(kg)
46321	5/16"	150	16.5	6	96	4.9
46322	3/8"	180	19.8	6	96	7.4
46323	7/16"	195	21.7	6	96	9.6
46324	1/2"	220	25.0	6	72	9.6
46325	9/16"	235	26.3	6	72	13.4
46326	5/8"	260	30.5	6	36	7.7
46327	11/16"	275	31.5	6	36	9.5
46328	3/4"	305	34.0	6	36	12.6

**XL X-BEAM® (METRIC)**

PART NO.	SIZE	L(mm)	A(mm)			G.W.(kg)
46301	8mm	150	16.5	6	96	4.9
46302	9mm	165	17.8	6	96	6.0
46303	10mm	180	19.8	6	96	7.4
46304	11mm	195	21.7	6	96	9.6
46305	12mm	207	23.0	6	96	11.1
46306	13mm	220	25.0	6	72	9.6
46307	14mm	235	26.3	6	72	11.7
46308	15mm	250	28.7	6	72	13.4
46309	16mm	260	30.5	6	36	7.7
46310	17mm	275	31.5	6	36	9.5
46311	18mm	290	32.5	6	36	10.3
46312	19mm	305	34.0	6	36	12.6

