





NUMBER 917659
METRIC

PRINT DIST
DIMENSIONS IN MM. DO NOT SCALE PRINT

AMP-J010-2C
REV.3/93



NOTE
1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER
COLOR:BLACK

~~2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON~~

注記
1 材料：ガラス入り熱可塑性ポリエステル樹脂
色：黒色

~~2 ハウジング全面にテフロン塗装のこと~~

	XX	1-917659-8
	XY	3-917659-6
	YY	2-917659-6
	XX	1-917659-6
	XY	3-917659-5
	YY	2-917659-5
	XX	1-917659-5
キーイングパターン KEYING PATTERN	キー KEY	型番 PART NUMBER

		20	62.86	59.66	54.8	45.72	9	1-917659-8
OBSOLETE								7-917659-6
OBSOLETE								6-917659-6
OBSOLETE								5-917659-6
								3-917659-6
								2-917659-6
		12	42.54	39.34	34.48	25.4	5	1-917659-6
OBSOLETE		10	37.46	34.26	29.4	20.32	4	7-917659-5
								3-917659-5
								2-917659-5
		10	37.46	34.26	29.4	20.32	4	1-917659-5
	FINISH POS.	A	B	C	D	N		PART NUMBER

Copyright ©1995* タイコ・エレクトロニクス・アンプ株式会社		Copyright ©1995 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.		Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan	
B2	OBSOLETE P/N. ECR-08-006764	Y.Y.D.M	14/MAR 2008	配線範囲(WIRE RANGE)	絶縁径(INSTULATION DIA.)
B1	ADD P/N. (FJ00-1259-00)	D.M.S.M	11/OCT '00	mm ² (AWG -)	mmφ
B	REVISED (FJ00-1130-97)	K.I.N.M	24/OCT '97	材料(MATERIAL) 注記参照 SEE NOTE	仕上(FINISH)
A	REVISED (FJ00-5656-96)	K.I.Y.I	1/NOV '96	DR. 14/APR/95 K.K.KEDA	DE. 14/APR/95 K.K.KEDA
O	RELEASED (FJ00-2158-95)	K.I.S.M	18/APR '95	CHK. 18/APR/96 S.Manabe	APP. 18/APR/96 S.Manabe
LTR	変更 (REVISION RECORD)	DR	CHK	DATE	
				名称(NAME) ダイナミック D3200 リセハウジング DYNAMIC D3200 REC HSG (DOUBLE ROW)	
				一般公差 (GENERAL TOLERANCE) 10mmF : ±0.2 10mmE 30mmF : ±0.25 30mmE 100mmF : ±0.3 100mmE : ±0.3	
				A3 J 917659 尺取(SCALE) 2-1 REV. B2 SHEET 1 OF 1	

(CUSTOMER DRAWING) 顧客用図面