



NUMBER 176143

3rd ANGLE PROJECTION

METRIC







PRINT DIST
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

AMP-J
REV. 4/83
FJ029188



1. 嵌合相手品番 : 176146
2. 製品規格 : 108-5294

1. MATING PART NUMBER : 176146
2. PRODUCT SPECIFICATION : 108-5294



ブラケット推奨寸法図
RECOMMENDED DIMENSIONS OF BRACKET
SCALE 4 : 1

LIGHT GRAY	6-176143-6
DARK GRAY	176143-6
BLACK	176143-2
色 (COLOR)	項番 (P/N)

										AMP Kawasaki, Japan		AMP AMP (JAPAN), LTD. Tokyo, Japan							
										WIRE RANGE mm ² CAVG -)		INSULATION DIA mm		NAME .187 SERIES SEALED CONNECTOR 2Pos. CAP HOUSING ASSY					
										MATERIAL PBT		COLOR 表参照 (SEE TABLE)		GENERAL TOLERANCE		SIZE C	LOC J	NUMBER C-176143	
B 変更 (REVISED) FJ00-1278-99 TS KB 21JUL 10/21/92										DR. G. Kinoshita 11/2/91		DE. G. Kinoshita 11/2/91		0<≦ 10 : ±0.2 10<≦ 30 : ±0.25 30<≦ 100 : ±0.3 ANGLES : ±3°					
A 変更 (REVISED) J-1668 MT KT 10/21/92										CHK K. Baba 11/12/91		APP. S. Ishikawa 11/12/91				SCALE 2-1	REV. B	SHEET 1 OF 1	
O 作成 (RELEASED) J-483 YK KO 11/12/91																			
LTR REVISION RECORD DR CHK DATE																			

CUSTOMER DRAWING