

# Product Information



## 5520UAI075L51-11

EAN 4031582310627

Swivel castor, housing made of Polyamide, with blind hole for furniture fittings.

Wheel centre made of Polyamide, Tread: Polyurethane, plain bearing

Technical Data	
Wheel diameter	75 mm
Width of Tread	10 mm
Castor width	65 mm
Centre hole	11 mm
Dome-Ø	45 mm
Swivel Interference	146 mm
Overall height	88 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.29 kg
Swivel Radius	73 mm
Hardness of tread	A 87 Shore
Load capacity	100 kg
Load capacity (static)	200 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

# Product Information



**5520UAI075L51-11**

EAN 4031582310627

