

Specifications for BMP71 Label Printer with QWERTY keyboard - UK Power Supply - 240V

Application	Electronic & General Labelling; Laboratory Identification; Safety Identification; Wire & Cable Marking
Article No.	710600
Built-in Symbols	500+ symbols included
Colour Capability	Monocolour
Continuous vs Die Cut Labels	Continuous Tape & Die Cut Labels
Keyboard Type	QWERTY
Description	The BMP™71 – Mobile Label Printer is a high end portable cable and wire label printer. As well as being the ideal cable and wire printing solution for the telecom/datacom and electrical markets, the BMP71 is also perfect for printing health and safety signs and labels in the process industries. The flagship of Brady's portable printer range, it reinforces our brand image as manufacturers of high performance, industrial and professional products as well as strengthening Brady's position as the technology leader in our chosen market.
Order Reference	BMP71-QWERTY-UK
PC Connectivity	USB
Portability	Yes
Print Speed (mm/sec)	38
Print Technology	Thermal Transfer
Size - Depth (mm)	332.7
Size - Height (mm)	116.80
Smart Cell	Yes
Additional Information	Printer, Hard Carry Case, 2 Label Rolls, 1 Black Ribbon Cartridge, Rechargeable Battery Pack, AC Adaptor, USB Communications Cable, TLS2200® / HandiMark™ Material Roll Adaptor, Quick Start Guide, Product CD (w/ Printer Driver, Tutorials, Full User's Guide), Cleaning Kit
Stand Alone Printing	Yes
Total Qty per Pack	1 Piece(s) / Piece
Weight (kg)	2.49
Max. Label Width (mm)	50.8

