



ENGLISH

Datasheet

Straight multi-purpose stainless shears

RS Stock number 450-3474



Material:

Stainless steel sheet for pliers, for rivet, spring steel for tension return spring, p.p injection handle

Finish:

Grinding cutting edge, fully polish finish for whole body

Hardness:

Heat treated to hrc: 50-54 degree (body)

Contents:

1 pc- 7-1/2" stainless steel straight type multi-purpose shears with red color p.p injection handle, light duty return coil spring, safety catch ocker is included. it fits to cut small wire, wood stickers, cardboard, rope, plastic cards and fabrics (overall length- 7-1/2"(190mm), serrated cutting length- 1-5/8"(42mm) & thickness-3.0mm)