





© COPYRIGHT — BY —

REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			S1	REVISED PER ECO-11-005294	08APR11	HMR



350919-3	PRE-TIN	.012 PH. BRZ	350874-3
		.012 BRASS	
—	PRE-TIN		350874-1
LOOSE PIECE (REF)	FINISH	MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±	CONTRACT NO DR <i>m. Feher 4-22-81</i> CHK <i>D.S. Weide 4/9/81</i> APPD <i>R. Polachuk 6-10-81</i> APPD DSGN APPD OTHER APPD
WIRE RANGE 18-14 AVVG INSULATION RANGE .200 DIA MAX	

TE TE Connectivity		
NAME SOCKET, UNIVERSAL MATE-N-LOK™		
SIZE B	CODE IDENT NO 00779	DRAWING NO 350874
SCALE 4-1		SHEET —