





	Innenleiter / inner conductor	CuZn39Pb3 / CuPb1.15Ni1	Cu1Ni2Au0.8 (c)
	Außenleiter / outer conductor	CuZn39Pb3	Cu2Ni5
	Isolierung / insulator	PTFE	
	Lötanschluß / soldering part	CuZn39Pb3	CuSnZn3
(b)	sonstige Metallteile / other metalparts	GD-ZnAl4Cu1	Zn/Cu8 Ni6 gl
	Montagebohrung / panel piercing	Z06	

c b a	12192 3766 2948	14.12.00 03.06.92 07.02.91	MA MaH JB	91	Datum/date	Name/name	Werkstoff/ material
				gez./drawn	25.01.	Bu	
				gepr./appr.	05.02.91	JB	Oberfläche/ finish
				Norm/stand.			
				Maßstab/scale	Benennung/title		
2:1	BNC–Winkelbuchse für gedruckte Schaltungen						
untol. Maße/ dim. without tolerances according to	Unterl./doc.type	Zeichnungsnr./drawing no.		 Maße/dimensions: mm			
	K	J01003A0030					
Änd./rev. Index	Änderungsmittelung/ revision code	Datum/ date	Name/ name		Original: DIN A4		
				Ersatz für/ replaces			

